# FOR YOUR BEST QUALITY CONTROL WITH THE ADVANCED MEASURING TOOL



**Industry Standard for handheld devices** 

## TESLA METER TM-801



Large improvement of performance! And keeping the usability of TM-701!

We have sold 15,000 pcs. of Tesla Meter TM-701 for about 6 years. We studied the demand of customers in those 6 years and refined it. Tesla Meter TM-801 is following TM-701 with major improvements.

Specifications and main features (for the comparison with previous model TM-701.)

#### The wide expanded range of measuring!

- Mode Accuracy of high resolution for measurement on DC magnetic flux density, is now improved.
- ullet Range covering frequency for measuring AC magnetic flux density is expanded.(40  $\sim$  500Hz)

## Max.160 hours of operating time & high speed sampling!

- ●Sampling speed is improved 1.5 times when measuring in the hold mode.
- Measuring time increases 20% for continuous operation with alkali batteries.
- Tesla Meter can be operated with batteries, chargeable batteries and AC power supply.

## Simple operation with your PC!

 Measured data is now read by your computer with outer digital output though USB



New free sample software is newly produced to respond with Windows XP/7/8.

#### [Application]

- Measurement of residual magnetism in machined parts, in stamped parts, and in demagnetized parts.
- Measurement of magnetic flux in magnets and magnetism applied products.
- Measurement of magnetic flux of motors.
- Measurement of properties of magnetic materials.

#### Reliability

 Measured data is now "mT" exclusively in compliance with the unit specified by the Measurement Law.



INPUT TERMINAL FOR AC POWER SUPPLY



INPUT TERMINAL FOR USB

#### TM-801 Features

							[mm(in)]	
Model	TM-801			Function	Zero reset Polarity indication			
Model				Function	Max. detect value hold	Auto power off (can be canceled)		
Detecting Contents	DC magnetic flux density AC magnetic flux density Polarities (N, S) (40~500Hz)				Output	USB communication port /output(analog)		
					Mode	Detection value	Numeric value (digital)	
Measuring	mT			Polarity		Alphabets (N/S)		
Indication Range	0—3000.0mT				Operating Temperature	0—+40°C (104° F)		
Measuring Mode	Measuring	Measuring range	Resolution	Indication accuracy	Power Source	Battery SUM-3(1.5 V) × 4 pieces DC5-6V adapter input/ USB  Height 140 (5.51) × width 64 (2.51) × thickness 30 (1.18)		
	mode	10.00		5 	Dimensions			
Measuring Range	DC× 1*	0— 200.0 mT	0.1 mT	$\pm$ (5% of rdg.+ 3digit)	Mass	Approx. 250 g/0.55 lb (including batteries and probe)		
Weasuring Hange		200.1—3000.0 mT	1 mT	$\pm$ (5% of rdg.+10digit)				
Resolution	DC×10	0— 300.00mT	0.01mT	± (3% of rdg.+ 5digit)		Epocycia Connect (Manual Millagle Connect (Blanch Case)		
	AC*	0— 150.00mT	0.01mT		Accessories	Probe, batteries and carrying case		
Indication Accuracy		150.1— 300.0 mT	0.1 mT	± (5% of rdg,+20digit)	0.11	Axial probe (TM-801AXL)		
		301.0—1500.00mT	1 mT		Option Reference magnetic field for Tesla Meter(TM-SMF)		sla Meter(TM-SMF)	

\* The measuring ranges are automatically selected.

Note: This product is not designed for measurement of electromagnetic waves.

#### Option / Accessories

#### MODEL TO MEASUREMENT PROBE FOR



A probe dedicated to TM-801. Please keep this probe as a spare; it can be replaced without troublesome calibration. In addition to the standard PRB (transverse type), an axial type (AXL) capable of measurement in the vertical direction and having higher durability is optionally available.

L(ul)mm1						
Model	Applicable Model	Tip Dimensions	Cord Length	Mass		
TM-801PRB		(T)10(0.03)×(W)3.5(0.13)×(L)65(2.55)	1000	50g/0.11 lb		
TM-801AXL	Only for TM-801	φ13 (0.51) ×55 (2.16)		(Including probe cap)		

\*Can be used with Kanetec,s conventional TM-501,TM601 and TM-701.

### Model TM-SMF REFERENCE MAGNETIC FIELD FOR TESLA METER

#### For calibration or dailycheck of the Tesla meter



[Application]

- Daily check of the Tesla meter.
- Calibration of the Tesla meter.

[Features]

- The closed circuit construction employing a permanent magnet that causes less magnetic force leak.
- Small and light weight.
   Usable with Kanetec TM-201 and above.



Model	Magunetic	Dimens	sions	Mass		
Model	Flux Density*	Frame Dia.	Height			
TM-SMF- 003	3mT		50(1.96)	Approx. 0.2kg/0.44		
TM-SMF- 050	50mT	φ43(1.69)	40(1.57)	Approx. 0.2kg/0.44 IU		
TM-SMF- 300	300mT		30(1.18)	Approx. 0.1kg/0.22 lb		
TM-SMF-1000	1000mT	φ73(2.87)	74(2.91)	Approx. 2.0kg/4.4 lb		

TM-SMF-050

\*Can be used with Kanetec,s conventional TM-501,TM-601 and TM-701.

In case reference magnetic field coresponding to Axial type probe TM-801AXL isrequired, please consult with us.

#### Model PC MAGNETIC POLARITY CHECKER



## Easy check of residual magnetic flux density, and N or S magnet polarity!

#### Application

In addition to selecting magnetic material, or to confirm the magnetic pole when magnet is installed, it can be used as an easy checker for residual magnetic flux density level on processed products.

[Features]

•Card size thickness, 6mm only. Convenient to have with you.

Audio tone and LED lights

N Pole (red LED) tone sounds in a short continuous note. S Pole (blue LED) tone sounds in a longer continuous note

• It detects magnetic flux density of more than 1mT so it can be used for simple confirmation of demagnetized results.
\*for precise measurement of magnetic flux density, please use TM-801 Tesla Meter

[mm	(in)	1

[mm(in)]

Model	Dimentions	Distinction Accuracy	Indication Lamp	Battery	Mass	Accessories
PC-10	55(2.16)×85(3.34)×t6(0.23)	N/S Approx. 1mT or more	N pole(Red LED) S pole(Blue LED)	CR2025 Button battery(included)	25g/0.055 lb	soft case

#### **UNION Market Enterprise Company LTD.**

1F., No.2, Alley 6, Lane 423, Zhuangjing Rd., Xinyi District,

Taipei City 110, Taiwan

TEL: 02-2722-1198 FAX: 02-2722-1120 Web site: http://www.umarket.com.tw E-mail: service@umarket.com.tw

%The products listed in this catalog are subject to change in models, appearance and specifications without notice.

14.10.04 (DM)